

RV5 ROTARY VANE PUMP

5.8 m³h⁻¹, 3.4 ft³min⁻¹, 96.7 l min⁻¹




TECHNICAL DATA


Displacement	
50 Hz operation	5.8 m ³ h ⁻¹ / 3.4 ft ³ min ⁻¹
60 Hz operation	7.0 m ³ h ⁻¹ / 4.1 ft ³ min ⁻¹
Speed (Pneurop 6602)	
50 Hz operation	5.1 m ³ h ⁻¹ / 3 ft ³ min ⁻¹
60 Hz operation	6.2 m ³ h ⁻¹ / 3.6 ft ³ min ⁻¹

GAS BALLAST	ULTIMATE VACUUM (TOTAL PRESSURE)	
	HIGH VACUUM MODE	HIGH THROUGHPUT MODE
Closed	2 x 10 ⁻³ mbar / 1.5 x 10 ⁻³ Torr	3 x 10 ⁻² mbar / 2.3 x 10 ⁻² Torr
Low flow, I	3 x 10 ⁻² mbar / 2.3 x 10 ⁻² Torr	6 x 10 ⁻² mbar / 4.6 x 10 ⁻² Torr
High flow, II		1 x 10 ⁻¹ mbar / 9.1 x 10 ⁻² Torr


Inlet connection	NW25
Outlet connection	NW25
Maximum allowed outlet pressure	1 bar gauge / 14 psig
Maximum allowed inlet and gas ballast pressure	0.5 bar gauge / 7 psig
Maximum water vapor inlet pressure	50 mbar / 38 Torr
Maximum water vapor pumping rate	
Gas ballast low flow	60 g h ⁻¹
Gas ballast high flow	220 g h ⁻¹
Motor power	
50Hz	250 W
60Hz	300 W
Electrical supply	
1-phase	110-120 V or 220-240 V, 50 or 60 Hz
3-phase	200-230 V or 380-460 V, 50 or 60 Hz
Operating temperature range	12 - 40 °C
Weight, without oil	21.5 kg / 43 lbs
Noise	48 dB(A)@ 50 Hz
Oil capacity	
Maximum	0.7 liter
Minimum	0.42 liter
Recommended oil (supplied)	Ultragrade 19



- 1 50 Hz high vacuum mode, gas ballast = 0
- 2 50 Hz high throughput mode, gas ballast = 0 and high vacuum mode, gas ballast = 1
- 3 50 Hz high vacuum and high throughput modes, gas ballast = 1



- 1 60 Hz high vacuum mode, gas ballast = 0
- 2 60 Hz high throughput mode, gas ballast = 0 and high vacuum mode, gas ballast = 1
- 3 60 Hz high vacuum and high throughput modes, gas ballast = 1



- 1 1-phase motor
- 2 3-phase motor
- 3 Retractable handle